# Product Data Sheet Luminy® LX530 with suffix BMB and RMB



**Revision date** 23 May 2023 **Page** 1 of 3 **Version & language** 2/0978 - EN **Product availability** Global

Commercial

PRODUCT DATA SHEET **LUMINY® LX530 with suffix BMB and RMB** 

Interested in solutions for bioplastics? Please contact us at

www.totalenergies-corbion.com pla@totalenergies-corbion.com

### DESCRIPTION

**Product status** 

PLA is a biobased polymer derived from natural resources and offers a significant reduction in carbon footprint compared to oil-based plastics. Luminy® LX530 with suffix BMB and RMB is a medium flow, fiber-grade resin suitable for staple fiber or spunbond applications.

#### TYPICAL PROPERTIES!

Physical properties	Method	Typical value
Density (literature value)		1.24 g/cm <sup>3</sup>
Melt flow index <sup>2</sup>	ISO 1133-A (210°C/2.16kg)	23 g/10 min
Melt flow index <sup>2</sup>	ISO 1133-A (190°C/2.16kg)	10 g/10 min
Stereochemical purity	TotalEnergies Corbion method	98% (L-isomer)
Appearance	Visual	Crystalline white pellets
Residual monomer	TotalEnergies Corbion method	≤ 0.3%
Water / moisture	Coulometric Karl-Fischer	≤ 400 ppm
Melting temperature	DSC	165°C
Glass transition temperature	DSC	60°C
Recycled content	Mass balance	20%
Mechanical properties	Method	Typical value
Tensile modulus	ISO 527-1	3500 MPa
Tensile strength	ISO 527-1	50 MPa
Elongation at break	ISO 527-1	≤ 5%
Charpy notched impact, 23°C	ISO 179-1eA	≤ 5 kJ/m²
	ISO 75-1	60°C

# PROCESSING INFORMATION AND RECOMMENDATIONS

Luminy® LX530 with suffix BMB and RMB can be processed on conventional extrusion spinning and drawing equipment. Thorough cleaning is highly recommended due to the incompatibility of PLA with a wide variety of polymers. In case of spinning PLA after another polymer resin, it is recommended to not install the spin pack until an even homogeneous flow of PLA is observed. Pre-drying of the resin is recommended. Typical melt spinning temperatures are 220-240°C.

# MOISTURE AND PRE-DRYING

It is recommended to dry Luminy LX530 with suffix BMB and RMB from the packaging for 4-6 hours at 85°C. Drying of standard PLA can be performed in a desiccant hot air dryer, with a dew point of -40°C or less. It is recommended to reduce the moisture content before melt processing to a level less than 250ppm and preferably less than 100 ppm, measured by e.g. Karl-Fischer or Brabender aquatrac method. Predrying is in particular important prior to injection molding, film and sheet production. Moisture causes hydrolysis of the PLA polymer during melt processing, resulting in reduced mechanical performance in the final part.





For crystalline resins, formulation included 3-7% nucleating agent (Luminy® D070) and molding took place in a 90-100°C tool

# Product Data Sheet Luminy® LX530 with suffix BMB and RMB



 Revision date
 23 May 2023

 Page
 2 of 3

 Version & language
 2/0978 - EN

# **PACKAGING & STORAGE CONDITIONS**

Luminy® LX530 with suffix BMB and RMB is available in 1250 kg form-stable aluminum-lined big bags. It is recommended to store PLA polymer in its closed, original moisture-barrier packaging at temperatures below 50°C. Storage in direct sunlight should be avoided. The supplied PLA polymer pellets are typically semi-crystalline, unless otherwise stated.

#### **COMPOSTABILITY**

Composting of organic waste helps to divert organic waste from landfill or incineration. Composting is a biological process in which organic wastes are degraded by microorganisms into carbon dioxide, water and humus, a soil nutrient. Luminy® PLA polymers are in compliance with the EN-13432 standard. Luminy® LX530 with suffix BMB and RMB has been certified compostable by TUV Austria (OK Compost S478) and by European Bioplastics (Seedling 7W2030) up to a thickness of 2.3 mm. As the compostability of the end product is also dependent on the geometry of product, it is the responsibility of the manufacturer of the end product to ensure compliance with the regulations.





#### **BIOBASED CONTENT**

Luminy® LX530 with suffix BMB and RMB has a biobased content of 100% (confidence level 1) and a biobased carbon content of 100% according to EN16785-1 under certificate number DIC-00001. Luminy® LX530 with suffix BMB and RMB is certified 100% biobased according to ASTM D6866 under the USDA Biopreferred program.





# RECYCLED CONTENT

Luminy® LX530 with suffix RMB contains recycled content from a combination of post-industrial and post-consumer PLA waste sources. The number behind the suffix is the allocated percentage of recycled content, e.g., RMB20 contains 20% recycled content, RMB30 contains 30% recycled content, etc. The recycled content is added via a chemical recycling process and is allocated using the principles of mass balance.

# **BONSUCRO CONTENT**

If Luminy® LX530 has suffix BMB, it is produced from 100% Bonsucro certified raw materials. The principles of mass balance have been applied with respect to Bonsucro chain-of-custody certification.

# **FOOD CONTACT STATUS**

In the European Union, Luminy® PLA polymers are compliant with EU commission regulation 10/2011 of 14 January 2011 (and amendments) on plastic materials and articles intended to come into contact with food. Lactic acid is considered a dual use substance, since lactic acid is approved as a food additive (additive number E270). There are no SMLs or SML(T)s for the ingredients used to produce Luminy® PLA. The regulation does include an migration limit of 10 mg/dm2 on the overall migration from finished plastic articles into food. It is the responsibility of the manufacturer of the final product, when intended as a food contact product, to determine that the use of the product is safe and also suitable for the intended application. While it is TotalEnergies Corbion's conclusion that the above mentioned polymers are permitted, it is the final product which must meet the given regulations and the manufacturer should take responsibility to check if the final product is in compliance with these regulations.





# Product Data Sheet Luminy® LX530 with suffix BMB and RMB



 Revision date
 23 May 2023

 Page
 3 of 3

 Version & language
 2/0978 - EN

In the United States of America, Luminy® PLA as supplied by TotalEnergies Corbion has been evaluated and was found to be suitable for use in food contact applications. On 30 November 2018, FCN 001926 as applied for by TotalEnergies Corbion to the FDA became effective. It is included in the list of effective notifications for FCNs on the website of the FDA. The evaluation performed was in line with the requirements of Section 201(s) and Section 409 of the Federal, Drug and Cosmetic Act, and Parts 182, 184 and 186 of the Food Additive Regulations. Luminy® PLA neat resin is approved for all food types and conditions of use B through H.

#### **NOTICE REGARDING USE RESTRICTIONS**

Unless specifically agreed to in writing, TotalEnergies Corbion will not knowingly market any product into any of the following commercial or developmental applications: (1) bottles or preforms, unless specific arrangements on recycling and end-of-life are in place, (2) microbeads used in personal care products, including without limitation, cosmetics or over-the-counter drugs, (3) components of products intended for human or animal consumption or (4) any application that is intended to be used inside the human body.



